



# Beetek

## HoneyMax™ Frame



- Faster and cleaner extraction due to large cell size
- Unique pink colouring for easy identification - ensures the frames are only used in your honey boxes
- Fewer cells per frame, therefore faster comb production, using less beeswax and less honey used to produce that beeswax
- Extraction trials have shown an extra 110 grams of honey extracted per frame

Field tested and proven by beekeepers throughout New Zealand, the new Beetek HoneyMax™ Frame is an evolution in honey extraction. The larger cell sizing (7.1mm compared to 5.4mm) allows honey to release more freely during extraction resulting in cleaner frames and more importantly improved yields. Extraction trials have shown an extra 110 grams of honey extracted per frame! With its eye catching pink colouring, the Beetek HoneyMax™ Frame is easily recognisable to ensure it stays in your honey boxes.

0800 11 77 66  
[ecrotek.co.nz](http://ecrotek.co.nz)

 **ECROTEK**  
*Keeping ahead*

# Product Information

|                 |                                       |                                     |
|-----------------|---------------------------------------|-------------------------------------|
| Order Code      | FRAPFDPWAX30G                         | FRAPFDP                             |
| Description     | Beetek Honeymax™ Pink Frame 30g Waxed | Beetek Honeymax™ Pink Frame Unwaxed |
| Material        | 100% pure virgin food grade resin     |                                     |
| Storage         | Store out of direct sunlight          |                                     |
| Carton Quantity | 54                                    |                                     |
| Pallet Quantity | 864                                   |                                     |

## ***What Our Customers are Saying***

"We trialed some of the new Beetek HoneyMax™ Frames from Ecrotek earlier this year and were really impressed with the results.

Extracting thixotropic Manuka using our conventional uncapper and without the use of a pricker, the HoneyMax frames extracted every bit as well as clover honey from regular frames, both cleanly and with less honey left in the cells. We have now purchased a much larger number of these for this season as a way to improve our apiary operations." - ***South Island Commercial Beekeeper***